

**Crimping tool
HTF 48**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

**Crimping tools for flat blade connectors and flat blade receptacles with open or rolled crimping claw**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With end stop for exact positioning of the contacts

General ordering data

Type	HTF 48
Order No.	9013080000
Version	Crimping tool, Crimping tool for contacts, 0.5mm ² , 2.5mm ² , B-Crimp
GTIN (EAN)	4008190113056
Qty.	1 pc(s).

Crimping tool HTF 48

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	200 mm	Weight	438 g
Net weight	453.98 g		

Technical data

Version	Mechanical, without interchangeable inserts
---------	---

Contact description

Type of contact	F-plug / -sleeve	Crimping range, min.	0.5 mm ²
Crimping range, max.	2.5 mm ²	Plug width	4.8 mm

Tool data - crimping

Crimping profile 1, min.	0.5 mm ²	Crimping typerofile	B-Crimp
Wire end ferrules cross-section, min.	0.5 mm ²	Crimping profile 1, max.	1 mm ²
Wire end ferrules cross-section, max.	2.5 mm ²	Crimping profile 2, min.	1.5 mm ²
Crimping profile 2, max.	2.5 mm ²		

Classifications

ETIM 3.0	EC000168	UNSPSC	23-17-16-04
eClass 5.1	21-04-03-01	eClass 6.2	21-04-38-90
eClass 7.1	21-04-38-90		

Product information

Descriptive text ordering data	Additional accessories can be found in Chapter J
--------------------------------	--

Approvals

Approvals



ROHS	Conform
------	---------

Crimping tool HTF 48

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen

