

Crimping tool HTF SUB-D

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Crimping tools for SUB-D contacts

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With end stop for exact positioning of the contacts

General ordering data

Type	HTF SUB-D
Order No.	9013260000
Version	Crimping tool, Crimping tool for contacts, 28AWG, 20AWG, FoderBcrimp
GTIN (EAN)	4008190056896
Qty.	1 pc(s).

Crimping tool HTF SUB-D

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	200 mm	Weight	438 g
Net weight	440.98 g		

Technical data

Version	Mechanical, without interchangeable inserts
---------	---

Contact description

Type of contact	SUB-D	Crimping range, min.	28 AWG
Crimping range, max.	20 AWG		

Tool data - crimping

Crimping profile 1, min.	28 AWG	Crimping typerofile	FoderBcrimp
Crimping profile 1, max.	24 AWG	Crimping profile 2, min.	22 AWG
Crimping profile 2, max.	20 AWG		

Classifications

ETIM 3.0	EC000168	UNSPSC	23-17-16-04
eClass 5.1	21-04-03-01	eClass 6.2	21-04-38-90
eClass 7.1	21-04-38-90		

Approvals

Approvals	
ROHS	Conform

Crimping tool HTF SUB-D

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen

