



Einhell

EXPERT Plus

TE-JS 18 Li - Solo

Cordless Jig Saw

The TE-JS 18 Li – Solo cordless jigsaw is a powerful tool for diverse sawing jobs. The selectable pendulum action and very smooth operation enable fast and precise cuts. The universal blade holder without tools saves valuable time, while the integrated plastic sliding element protects sensitive workpieces. The tool is supplied without battery and charger but it can be powered by Power X-Change rechargeable batteries.

Features

- Member of the Power X-Change family
- Very smooth operation for exact cutting
- Selectable pendulum action for fast cutting
- Universal blade holder without tools
- Includes dust blow-off function for optimum visibility
- LED light to illuminate the cutting area
- Integrated plastic sliding element for sensitive workpieces
- Additional attachable cutting line guide for exact cutting
- Complete with chip guard for cuts without splintering
- Supplied without battery and charger (available separately)



Technical Data

• Number of strokes	2400 min ⁻¹
• Stroke height	25.4 mm
• Cutting depth in wood	80 mm
• Cutting depth in plastic	12 mm
• Cutting depth in steel	10 mm
• Max. bevel cuts	47 °
• Toolless saw blade change	yes



Logistic Data

• Product weight	1.82 kg
• Gross weight single packaging	2.02 kg
• Dimensions single packaging	235 x 80 x 225 mm
• Pieces per export carton	5 Pieces
• Gross weight export carton	15 kg
• Container quantity (20"/40"/40"HC)	5080 11165 0



Illustrations can contain accessories, which are not included in standard extent of delivery
Illustration similar (in design), production-wise modifications reserved
GS mark belongs to the product itself only, excluded accessory