



Einhell

GE-CH 1846 Li Cordless Hedge Trimmer



The cordless hedge trimmer GE-CH 1846 Li is a high-value, high-performance device that proves in the independent power network care of stern, bushes and bush to be an indispensable helper. Through the new Power X-Change Battery Management System of Einhell, the hedge trimmer can be driven with an 18 V rechargeable battery with 1.5 Ah, for expanded uses without troublesome electric cable. Thanks to the practical ergonomic handle and the very low weight, an ergonomic and comfortable working is guaranteed.

Features

- Two hand safety switch with electric cutter stop < 1 sec (1)
- Aluminium cover on cutters (2)
- Bumper-guard with holder for wall hanging (3)
- Counter rotating double bladed safety cutters made of laser-cut and diamond cutter steel (4)
- Metal gear
- Sturdy bag for storage and transportation (not illustrated)
- Suitable for Power X-Change Battery System (not included in delivery)
- Low weight for easy handling

Technical Data

- | | |
|------------------------------|--------|
| ■ Cutting length: | 460 mm |
| ■ Cutter rail length: | 520 mm |
| ■ Tooth spacing: | 15 mm |
| ■ Cutting thickness approx.: | 11 mm |
| ■ Cuts per min.: | 2,200 |
| ■ Oerating time approx.: | 60 min |
| With Power-Pack 1.5 Ah | |
| ■ Product weight: | 2.2 kg |

Logistic Data

- | | |
|-----------------------|--------------------|
| ■ Net weight: | 2.2 kg |
| ■ Gross weight: | 2.8 kg |
| ■ Packing dimensions: | 1005 x 130x 170 mm |
| ■ Bar code: | 4006825 588293 |
| ■ Sales Unit: | 4 pcs |

baugleich
mit GH-CH 18 Li



baugleich
mit GH-CH 18 Li

