

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [22-55-2162](#)
Status: **Active**
Overview: [SL™ Modular Connectors](#)
Description: 2.54mm Pitch SL™ Crimp Housing, Dual Row, Version B, Polarized, 16 Circuits

Documents:
[3D Model](#) [Product Specification PS-70400 \(PDF\)](#)
[Drawing \(PDF\)](#) [Test Summary TS-70058-001 \(PDF\)](#)
[Product Specification PS-70058 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General

Product Family Crimp Housings
Series [70450](#)
Application Signal, Wire-to-Board
Comments Version B
Overview [SL™ Modular Connectors](#)
Product Name SL™
UPC 800754320313

Physical

Breakaway No
Circuits (maximum) 16
Color - Resin Black
Flammability 94V-0
Gender Female
Glow-Wire Compliant No
Material - Resin Polyester
Net Weight 1.400/g
Number of Rows 2
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 2.54mm
Stackable No
Temperature Range - Operating -40°C to +105°C

Material Info

Old Part Number 70450-0056

Reference - Drawing Numbers

Product Specification PS-70058, PS-70400
Sales Drawing SD-70450-0050-0075
Test Summary TS-70058-001



Series

image - Reference only

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[70450Series](#)

Mates With
2.54mm Pitch C-Grid® Header [70229](#) ,
[70280](#) , [70246](#) , [70247](#)

Use With
[70058](#) , [71851](#)