


MNX PC 95/35 LT



Sample photo

Order symbol: PC 95/35 LT
Product nbr: 6012931
Description: Enclosure, PC
Remarks: Smoked transparent cover

EAN: 6418074054654
EI. number:
 Finland: 3421368
 Electric No. 8212027695
 Denmark:
 Electric No. Sweden: 6012931

Including: Base with PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:	
mm:	100	100	35	MIN 8	DIN-15 Mounting rail
inch:	3.9	3.9	1.4	B-3	DIN-35 Mounting rail
				FP 22046	Wall fastening lug (4 pcs)

Materials:		Rating:
Material:	Polycarbonate	Ingress Protection (EN 60529): IP66/67
Base colour:	RAL 7035 -light grey	Impact Resistance (EN 62262): IK08
Cover screws material:	Polyamide	Electrical insulation: Totally insulated
Cover colour:	Smoked grey	Halogen free (DIN/VDE 0472, Part 815): 1
Cover screws colour:	Black	UV resistance: UL 508
Gasket material:	Polyurethane	Flammability Rating: UL 746C 5V
		Glow Wire Test (IEC 695-2-1) °C: 960
		NEMA Class: NEMA 1, 4, 4X, 6, 12, 13

Temperatures:		Certificates:
Temperature °C (short term):	-40 ... 120 °C	Germanischer Lloyd (GL)
Temperature °C (continuous):	-40 ... 80 °C	SGS Fimko
Temperature °F (short term):	-40 ... 250 °F	Gost R
Temperature °F (continuous):	-40 ... 175 °F	

Accessories:	
MIV 95	Mounting plate (Galvanized steel)

