

USB UK power supply 4.8A (Dual 2 x 2.4A)



General Spec

| | |
|--------------------------|------------------------|
| Part Numbers | SW4503-UK |
| Output | 4.8A max (2 x 2.4A) |
| Current Min. | 0.01A |
| Power (watts) | 24W |
| Line Reg | +/-5% at rated load |
| Total Output Regulation | +/-5 % at 10—100% load |
| Case Size | 60 x 60 x 31mm |
| Weight (approx.) | 200g |
| Output connection | USB Socket x 2 |
| Rated Input Voltage | 100-240Vac |
| Full Input Voltage Range | 90-264Vac |
| Rated Frequency | 50-60Hz |
| Full Frequency Range | 47-63Hz |
| Efficiency | Meets ErP stage 2 |
| | MEPS: V |
| | CEC V |

Description:

This high power USB power supply is rated to 4.8A max across 2 x 2.4A outputs. The unit meets latest ErP stage 2 (CEC V) requirements and has high reliability with M.T.B.F of 50K hours at 25 degrees C. The unit is suitable for fast charging a number of devices such as Apple and Android units, Sat Navs, MP3 players and more.

Full specification documents on each part included in this data sheet are available on request from PowerPax UK Ltd. PowerPax accepts no responsibility for typographical errors in the production of this leaflet. Product specifications are subject to change without notice

