

## UL/CSA Hook-Up Wire

### UL Style 1061, CSA Type AWM I A/B



#### Product Type:

UL Cable

#### Application:

These single core cables are mainly used in the internal wiring of electrical and electronic equipment. They are manufactured and approved to UL and CSA specifications

#### Standards:

UL Style 1061

CSA Type AWM I A/B

Vertical flame propagation: complies with CSA FT-1; UL VW-1.

REACH and RoHS Compliant

#### Construction:

Conductor:	Tinned annealed copper to UL Subject 758
Insulation:	PVC compound meeting the requirements of: <ul style="list-style-type: none"> <li>Special (Semi-rigid) PVC to UL Subject 758</li> <li>Class 24 to CSA Standard C22.2 No. 210</li> </ul>

#### Electrical Characteristics:

Rated Voltage 300V  
 Rated Temperature 80 °C

#### Physical Characteristics:

Conductor Size (AWG)	Minimum insulation resistance at 90°C (MΩ/Km)	Max. Overall Diameter (mm)	Weight (Kg/Km)
26	0.013	1.05	2.1
24	0.013	1.15	2.9
22	0.013	1.30	4.3
20	0.013	1.50	6.5
18	0.013	1.80	9.3

Datasheet Ref: UL\_Style\_1061

Issue: 1

Page 1 of 1

This data sheet remains the property and copyright of C & C Cables Limited and the information contained within this document must not be copied or reproduced without the permission, in writing, from C & C Cables Limited. All information contained within this data sheet was correct at time of creation but may be subject to change without prior notice.

**C & C Cables Limited** Unit OA, Time Technology Park, Blackburn Road, Simonstone, Burnley, Lancs, BB12 7NQ, UK