

## Professional Address Label Printer with Plug and Print



The arrival of the QL-700 Labeller makes label printing faster, easier and more affordable than ever before whether you're producing address labels, CD/DVDs, ID passes or barcode labels.

Its compact size belies its big capability for performance, with the capacity to produce up to 93 labels a minute. Speed is just as impressive when it comes to setup, with no installation of drivers or software necessary for hassle-free plug and print usage.

For professional results every time, an integral auto cutter cleanly trims bespoke sizes quickly when using the continuous tape leaving you more time to design the ideal original label for the job. Or simply choose from the supplied suite of template designs for home or office applications. And with an SRP of just £129 Ex Vat, the QL-700 Labeller is also priced to move very fast.

### Key Features

- Save time up to 93 labels per minute print speed
- Durable Automatic cutter
- Save time - Print labels instantly with plug and print
- Versatile – Choose from a range of pre-sized and continuous labels for different applications
- print address labels directly from Microsoft Word, Excel and Outlook
- Space-saving – compact size

### Supplies

#### Die Cut labels

Standard address label (400)	29 x 90mm	DK-11201
Large address label (400)	38 x 90mm	DK-11208
Small address label (400)	29 x 62mm	DK-11201
Shipping label (400)	62 x 100mm	DK-11201
File folder label(400)	17 x 87mm	DK-11201
Multi-purpose label (400)	17 x 54mm	DK-11201
Square label (400)	23 x 23mm	DK-11201
CD/DVD label (400)	58mm	DK-11201
Round Label (400)	12mm	DK-11201
Round Label (400)	24mm	DK-11201

#### Continuous-length labels (30.48 meters)

12mm	DK22214	29mm	DK22210
38mm	DK22225	50mm	DK22223
62mm	DK22205		
54mm	Non Adhesive		DKN55224
62mm	Removable (White)		DK44205
62mm	Removable (Yellow)		DK44605

#### Continuous-length labels (film 15.24 meters)

29mm	DK22211	62mm white	DK22212
62mm Yellow	DK22606	62mm clear	DK22113

### Optional Extras

- None available

## Product Specifications

<b>Housing Colour</b>	Black and White
<b>Key Board</b>	No
<b>Number of Keys</b>	4 (On/Off, Editor Lite, Feed, Cut)
<b>Cutter</b>	Durable Auto cutter (User irreplaceable)
<b>Auto Half Cutter</b>	No
<b>Power</b>	Internal S/W Power Supply
<b>LCD</b>	No
<b>LED</b>	2 (STATUS: 3 colour - Green, Red, Orange / Editor Lite: 1 colour - Green)
<b>Print Method</b>	Thermal
<b>Print Head</b>	300 dpi / 720 dots
<b>Print Speed</b>	150 mm (5.9") / sec / 93 standard address labels / min.
<b>Roll Type</b>	DK rolls (DK Die-cut Labels / DK Continuous Length Tape)
<b>Roll Width</b>	Max. Label width 62mm (2.4")
<b>Max. Print Width</b>	59mm (2.3") max.
<b>Printable Label Length</b>	12.7mm (0.5") - 1m (3')
<b>Printer Driver</b>	QL-700
<b>Computer Interface</b>	USB (Plug and Print)
<b>Label Editing Software</b>	Win: P-touch Editor ver. 5.0, P-touch Address Book ver. 1.1 Mac: P-touch Editor ver. 5.0
<b>Bar Code</b>	Software side: CODE39, CODE128, UCC/EAN128(GS1-128), ITF(I-2/5), CODABAR(NW-7), UPC-A, UPC-E, EAN13, EAN8, ISBN-2(EAN13 AddOn2), ISBN-5(EAN13 AddOn5), Laser Barcode, POSTNET, RSS(RSS14 Standard, RSS14 Truncated, RSS14 Stacked, RSS14 Stacked Omni, RSS Limited, RSS Expanded, RSS Expanded Stacked), PDF417(Standard, Truncate, Micro), QR code(Model1, Model2, Micro), Data Matrix(ECC Square, ECC Rectangular), MaxiCode(Model2, Model3, Model4, Model5)
<b>Add-in for Microsoft</b>	Win: Word, Outlook, Excel
<b>Database file compatibility</b>	Win: csv, txt, mdb, xls Mac: csv, txt

## Weights/ Dimensions/ Measures

Dimensions

128mm(W) x 221mm(D) x 153mm(H)

Weight

1.12kg (without DK roll)

## What's in the box

CD-ROM (P-touch Editor 5.0 for Windows, P-touch Address Book 1.1, P-touch Editor 5.0 for Mac, Printer Driver, User's Guide, Software User's Guide)  
Quick Setup Guide, DK Rolls Line-up Guide  
USB cable, Warranty card  
DK-11201 Standard Address Labels (100 labels)  
DK-22205 (62mm Continuous) Starter roll (8 m)  
Registration Insertion, AC Power cord, EEE insertion

