

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [15-97-9121](#)
Status: **Active**
Overview: Mini-Fit® TPA Plugs and Receptacles
Description: Mini-Fit® TPA Key for 12 Circuit

Documents:

[3D Model](#) [Packaging Specification PK-30072-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-5556-003 \(PDF\)](#)

General

Product Family	Crimp Housings
Series	30072
Application	Power, Wire-to-Board, Wire-to-Wire
Overview	Mini-Fit® TPA Plugs and Receptacles
Product Name	Mini-Fit® TPA
UPC	800754203104

Physical

Circuits (maximum)	12
Color - Resin	Natural
Gender	Female
Glow-Wire Compliant	No
Material - Resin	Nylon
Net Weight	0.256/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.20mm
Stackable	No
Temperature Range - Operating	-40°C to +105°C

Electrical


Current - Maximum per Contact	13A
-------------------------------	-----

Material Info

Old Part Number	30072-12
-----------------	----------

Reference - Drawing Numbers

Packaging Specification	PK-30072-001
Product Specification	PS-5556-003
Sales Drawing	SD-30072-*



EU RoHS

**ELV and RoHS
Compliant**

**REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
 non-product compliance questions.

Search Parts in this Series

[30072Series](#)

Mates With

[30068](#) , [30069](#) , [30069](#) , [30070](#) , [30070](#) ,
[44473](#)

Use With

[30067](#) 4.20mm Pitch Mini-Fit® Crimp
 Housing