## Shielded D-Sub Backshells DVZK Series

## **TECHNICAL SPECIFICATIONS**

Material: Zinc, Ni-plated
Temp. range: -40°C - 120°C
Cable strain relief: Polycarbonate

PC UL94 V-0

Cable diameter: 3.0 - 13.0 mm Locking screws: Long jackscrews

with moulded top for colour coding


Assembly screws: Taptite threadforming

Cable outlet: Angled


Attenuation factor: > 40 dB between 30 MHz


and 1 GHz











## PART NUMBERING SYSTEM

	DVZK15 -	- BULŁ
Series: ————————————————————————————————————		
9, 15, 25, 37 or 50 Thread (jackscrew): ————————————————————————————————————		
M2.6 M3.0 Packaging: ———— K = Kit package		

## **FEATURES**

BULK = Bulk / 100 pcs

- Available in sizes 9, 15, 25, 37 and 50
- Minimise interference from electromagnetic and RF sources
- Non-static parts avoid ESD problems
- Accept round foil and braided cable types
- Approved according VDE 0871, FCC 20780 and 89/336/EU
- Printed logotype available upon request
- Long jackscrews with UNC 4-40 thread as standard, M2.5, M2.6 or M3.0 as option
- For custom designed solutions, please consult factory