

Data Sheet
9-215 Spannfix for permanent mounting



Part number 9-215

The small vice SPANNFIX with the types 9-205, 9-215 and 9-220 as well as the VARIO combinations 9-251, 9-252, 9-253, 9-254, 9-255, 9-256, 9-257 simplifies the operations in precision engineering, in laboratories, in mechanical and electronical workshops as well as in different medical areas.

Furthermore the SPANNFIX bases enable an exact and secure adjustment in all directions, e.g. of measuring instruments, of monitors and of observation cameras.

For these purposes the types 9-251, 9-261, 9-262 und 9-281 are available.

The high grade powder-coated aluminium casting and the surface-refined steel parts are the guarantee for a long life.

Article description SPANNFIX for permanent mounting

Characteristics:

Practice tip Size of base 150 x 105 mm

Clamping pressure	1.470 N	
Clamping capacity	70 mm	
Clamping depth	38 mm	
Jaw width	50 mm	plastic jaws exchangeable Art.-No. 9-206-50

Weight 1.350 kg

Customs Tariff Number: 82057000

EAN Number: 4250838511247

Link to catalogue page: www.bernstein-werkzeuge.de/Katalogseiten/Spannfix_English.pdf

Link to image: <http://www.bernstein-werkzeuge.de/Artikelbilder/09/9-215.jpg>

Image file: 9-215.jpg

Keywords: Vice, Clamping vice, Spannfix