



T&B®

Rigid/IMC Conduit Fittings-Hazardous Location T&B Catalog Number:

UPC Number: GUAT26-TB
Status: 78621098177
Description: Active

3/4 in. GUAT Hazardous location Conduit Outlet Box, Box-Ductile Iron-Zinc Plated, Cover-Die Cast Aluminum, 13.3 cu.in.

Features

All hubs have a minimum of five full threads and integral bushing
 All boxes are furnished with internal grounding screw.

Application

GUA boxes can be used for hazardous location conduit runs for the following: (1) Allows for mounting of fixture outlets when used with appropriate covers; (2) Provides easy access to wiring; (3) Provides junction in conduit for wire pulling and splices; (4) Changes direction in rigid conduit systems; (5) Attaches two or more pieces of conduit long runs; (6) Guards against damage to wires in rigid conduit.

General

Material: Ductile Iron
Finish: Zinc Plated
Volume (cu.in.): 13.3

Dimension Information

Hub Size (inches): 3/4
Dimension A (inches): 2
Dimension B (inches): 3 1/2
Dimension C (inches): 7/8
Throat Diameter-Max (inches): 0.810
Throat Diameter-Min (inches): 0.755

Specifications

3dmodel: Available on Website

Packaging

Package in Units: 1
T&B Sold in UOM: Each
T&B Weight Per UOM: 223 lbs. per 100

Notes

***Note:** Class I, Div. 1&2, Groups C, D - Explosionproof
****Note:** Class II, Div. 1, Groups E, F, G - Dust-Ignitionproof
*****Note:** Class III, Div. 1&2 - Raintight
******Note:** NEMA 3, 4, 7 CD, 9 EFG - Wet Locations

Certifications

RoHS Compliance: No

Certifications



File Nbr:
E 202368

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com