



Sta-Kon®

Ring Terminal

T&B Catalog Number:

RD167

UPC Number:

78621065426

Status:

Active

Description:

Insulated Nylon Ring Terminal For Wire Range 8 Stud Size #8, Red

WEB_USE

US Cutsheet PDF Catalog Link

<http://www-public.tnb.com/contractor/docs/stakon.pdf>

Features

Funneled Barrel Entry, Deep Internal Serrations, Brazed or overlapping seams.

General

Insulation Type	Insulated Nylon
Terminal Series	RD
Material	Copper
Finish	Electro -Tin Plated
Color	Red
Wire Range	8
Stud Size	#8

Dimension Information

Maximum Insulation (inches)	.340
Stock Thickness	.04
A (inches)	1.48
B (inches)	.42
C (inches)	.28
M (inches)	1.29

Specifications

Temperature Rating	105°C
Voltage Rating	600V
Flammability Rating	UL 94 V-2

Tooling


Tool Charts	Available on Website
Application Tools	ERG4007
Recommended Tool	ERG4007

Packaging

T&B Order Multiple	200
T&B Inner Pack	200
Package in Units	2000
Package Type	Bulk
T&B Sold in UOM	Each
T&B Weight Per UOM	1.01 lbs. per 100

Application Support

T&B Sales Drawings	wsd-000208
Overview	Available on Website
Wire Guide Tables	Available on Website



Notes

Not available on Mylar Tape.

Certifications

RoHS Compliance

Yes

Certifications



File Nbr:

E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com