



T&B[®]

Rigid/IMC Conduit Fittings-Hazardous Location T&B Catalog Number:

UPC Number: 04226945380
Status: Active
Description:

1 in. Hazardous location External Hub with installed green ground screw, Die Cast Aluminum, 'T' Style, 18.8 cu in. Surface cover included.

Features

Precision cast and machined surfaces permit safer wire pulling.

Precision NPT threaded hubs allow trouble-free field installation for rigid or IMC conduit.

Die cast construction and industrial design combine to produce a rugged protective enclosure for devices on industrial and OEM applications.

Application

Junction for branch conduits in hazardous locations.

General

Material: Die Cast Aluminum
Volume (cu.in.): 18.8
Cover Opening (inches): 3 11/16

Dimension Information

Hub Size (inches): 1
Dimension A (inches): 4
Dimension B (inches): 2 1/4
Dimension C (inches): 2 15/16
Dimension D (inches): 1 3/8
Dimension E (inches): 11/16
Dimension F (inches): 11/16
Dimension G (inches): 5 1/2
Dimension H (inches): 5 9/16
Dimension J (inches): 4 3/16
Dimension K (inches): 3 5/16
Dimension L (inches): 9/16

Specifications

3dmodel: Available on Website

Packaging

T&B Inner Pack: 1
Package in Units: 5
T&B Sold in UOM: Each
T&B Weight Per UOM: 1.2 lbs. Each

Notes

***Note:** Class I, Div. 1&2, Groups C, D - Explosionproof
****Note:** Class II, Div. 1, Groups E, F, G - Dust-Ignitionproof
*****Note:** Class III, Div. 1&2 - Raintight

****Note

NEMA 3, 4, 7 CD, 9 EFG - Wet Locations

Certifications

RoHS Compliance

No

Certifications



File Nbr:

E 35010

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com