

8U, 12U or 22U Wall-Mount Open Frame Rack

MODEL NUMBER: **SRWO8U22**



Description

The Tripp Lite SRWO8U22 Wall-Mount Open Frame Rack is an expandable, two-post, wall-mount, 19-in open frame rack that can be assembled as an 8U, 12U or 22U all from same sku. Designed for securing high density servers and networking equipment, it can meet your current needs while leaving rack space in reserve for the future. The SRWO8U22 is designed with provisions to integrate wall mounting, easy equipment access and cable management. Its heavy-duty steel frame can accommodate up to 150 lbs. of equipment. The SRWO8U22 assembles and installs quickly, and comes with a five-year warranty. All required parts and assembly hardware are included.

Features

- **Expandable Open Rack:** Can be assembled as an 8U unit to meet current needs and expanded later to 12U or 22U to accommodate growth
- **Space-Saving:** It conserves valuable floor space, helps IT managers to better organize their equipment array and simplifies access for equipment installation and servicing
- **Non-Locking:** Ideal solution for secure IT environments and other applications not requiring a lockable enclosure
- **19-in Rack Compatibility:** Compatible with all standard 19-in. rack equipment that supports two-post mounting and a maximum mounting depth of 18 inches
- **High Capacity:** Supports up to 150 lbs. of wall-mounted, rack equipment
- **Easy Installation:** All the parts required to assemble an 8U, 12U or 22U two-post, wall-mounted, open frame rack

Highlights

- Wall-mount, open frame rack solution for applications where space is limited.
- Expandable—can be assembled as an 8U, 12U or 22U rack
- Compatible with all standard 19-in. equipment
- Heavy duty steel frame;150-lb. load capacity
- Easy assembly; all assembly hardware included

Package Includes

- (1) 3mm L-Shaped Hex Key
- (2) Top/Bottom Panel Frames
- (2) Short Vertical Mounting Rails
- (2) Long Vertical Mounting Rails
- (9) M5 Button Head Cap Screws
- (24) #12-24 Equipment Mounting Screws
- Expansion Kit (packaged separately)
- (1) 3mm L-Shaped Hex Key
- (2) Mounting Rail Tie Plates
- (9) M5 Button Head Cap Screws
- (8) Zip Ties

Specifications

SELECTOR	
Selector Type	RACK EQUIPMENT
General Info	



Product Group	RACKS
TAA Compliant	No
OVERVIEW	
Style	Wall Mounted
Rack Type	Wall-Mount; Open-Frame
PHYSICAL	
Installed Whole System Maximum Rack Depth (in.)	18
Installed Whole System Maximum Rack Depth (cm)	45.72
Rack Height (U Spaces)	8
Shipping Dimensions (hwd / in.)	3.03 x 20.28 x 18.70
Shipping Dimensions (hwd / cm)	7.69 x 51.51 x 47.49
Shipping Weight (lbs.)	16
Shipping Weight (kg)	7.25
Unit Dimensions (hwd / in.)	0 x 20.11 x 18.24
Unit Weight (lbs.)	13.77
Unit Weight (kg)	6.24
Unit Dimensions (cm)	EXTERNAL DIMENSIONS: 0 x 51 x 46.32 (HWD)
Color	Black
Weight Capacity - Stationary (lbs.)	150
Weight Capacity - Stationary (kg)	68.0
CERTIFICATIONS	
NOM (Mexico)	Tested to NOM (Mexico)
Approvals	EIA-310-D, IEC 60297-3-100, DIN 41494, RoHS
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty