

M39029/28-211

Deutsch - Machined Contact

38999 CON 12 COAX PIN SHIELDED



PRODUCT INFORMATION

Specification:	MIL-C-39029
Contact Style:	Coax Pin
Termination Method:	Crimp
Crimp Wire Gauge:	RG-174A/U, RG-316/U, RG-179B/U, RG-188A/U, RG-161/U, RG-187A/U
Contact Size:	#12
Contact Material:	Copper Alloy
Contact Plating:	50 microinches Gold Plate
Weight (lbs):	0.00123
Weight (g):	0.55600