

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [39-00-0041](#)  
**Status:** **Active**  
**Overview:** Mini-Fit Jr.™ Power Connectors  
**Description:** Mini-Fit® Male Crimp Terminal, Tin (Sn) over Copper (Cu) Plated Brass Contact, 18-24 AWG, Bag

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification PS-52034-004 (PDF)</a>
<a href="#">Product Specification PS-51010-005 (PDF)</a>	<a href="#">Product Specification PS-5556-002 (PDF)</a>
<a href="#">Product Specification PS-51010-006 (PDF)</a>	<a href="#">Test Summary TS-5556-002 (PDF)</a>
<a href="#">Product Specification PS-51096-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification PS-52034-003 (PDF)</a>	

**General**

Product Family	Crimp Terminals
Series	5558
Application	Power
Crimp Quality Equipment	Yes
MolexKits	Yes
Overview	<a href="#">Mini-Fit Jr.™ Power Connectors</a>
Packaging Alternative	<a href="#">39-00-0040 (Reel)</a>
Product Name	Mini-Fit®
UPC	800753585034

**Physical**

Durability (mating cycles max)	30
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	123.000/mg
Packaging Type	Bag
Plating min - Mating	0.889µm
Plating min - Termination	0.889µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.30-3.10mm
Wire Size AWG	18, 20, 22, 24
Wire Size mm²	N/A

**Electrical**


Current - Maximum per Contact	9A
Voltage - Maximum	600V

**Material Info**

Old Part Number	5558TL
-----------------	--------

**Reference - Drawing Numbers**

Product Specification	PS-51010-005, PS-51010-006, PS-51096-001, PS-52034-003, PS-52034-004, PS-5556-002, RPS-30067-002
Sales Drawing	SD-5558****
Test Summary	TS-5556-002



**EU RoHS**

**ELV and RoHS Compliant**  
**REACH SVHC Contains SVHC: No**  
**Low-Halogen Status Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[5558Series](#)

**Mates With**

[5556 Mini-Fit® Crimp Terminal](#)

**Use With**

[5559 Mini-Fit Jr.™ Plug Housing, 30068 Mini-Fit® TPA Plug Housing, 42475 Mini-Fit® BMI Plug Housing](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
Hand Crimp Tool for Male and Female Crimp Terminals, 16-24 AWG Wire	<a href="#">0638190900</a>
Extraction Tool	<a href="#">0011030044</a>

**Japan**

<b>Description</b>	<b>Product #</b>
Hand Extraction Tool	<u>0570316000</u>
Handtool (Straight Action)	<u>0570225500</u>
Hand Crimp Tool	<u>0570265000</u>

This document was generated on 12/18/2014

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**