



DISTRIBUTION BOARD

AK 14



AK 14

Distribution board

CUSTOMIZABLE

300 x 300 x 142 mm
Article number: 73541401

Distribution board, 1 row, 14 modules, screwless PE/N terminal rails each with 3 screwable clamping points, 2.5 - 16 mm², 14 screwless clamping points, 1.5 - 4 mm², elastic entries on top, with cable covering, masking and labelling strips, additional double-membrane seals and other accessories



Technical data

Measures

Width:	300 mm
Length:	300 mm
Height:	142 mm

Material

Base:	Polystyrene, grey, similar to RAL 7035
Cover:	Polystyrene, grey, similar to RAL 7035
Sealing:	Polyurethane
Cover screw:	Polyamide 6, fiber-glass reinforced

Accessory

- AK KS-IP65 - Combi set
- AK SGA-1 - Lock fittings
- BST M20 - Ventilation seal

Environmental attributes

Ambient temperature (min.):	-25 °C
Ambient temperature (max.):	40 °C
Ambient temperature (24 h):	35 °C
Max. rel. humidity at 25° C (short Therm):	95%
Max. rel. humidity at 40° C:	50%



DISTRIBUTION BOARD

AK 14

Other attributes

Color:	grey
Ingress protection:	IP65 - acc. EN 60529 / DIN VDE 0470-1
Number of distribution units:	14
Tackable:	Yes
Fire protection:	none
Heavy metals-free:	Yes
PVC-free:	Yes
Silicone-free:	Yes
sealable:	Yes