

LED PANEL MOUNT INDICATOR


PROMINENT BEZEL, DC OPERATION

MOUNTING HOLE, Ø 8mm

PART NO.	COLOR	VOLTAGE V _{OP} [V] DC	CURRENT I _{OP typ.} [mA] DC	LUMI. INTENSITY	DOMINANT
				LED I _{V typ.} [mcd]	WAVELENGTH λ _D [nm]
SATIN CHROME BEZEL					
WL-19040251	GREEN	12V	20	40	568
WL-19040252	YELLOW	12V	20	40	588
WL-19040253	RED	12V	20	80	625
WL-19040257	BLUE	12V	20	90	466
WL-1904025W	WHITE	12V	20	450	*
WL-19040351	GREEN	24V	20	40	568
WL-19040352	YELLOW	24V	20	40	588
WL-19040353	RED	24V	20	80	625
WL-19040357	BLUE	24V	20	90	466
WL-1904035W	WHITE	24V	20	450	*
WL-19040451	GREEN	28V	20	40	568
WL-19040452	YELLOW	28V	20	40	588
WL-19040453	RED	28V	20	80	625
WL-19040457	BLUE	28V	20	90	466
WL-1904045W	WHITE	28V	20	450	*
BLACK CHROME BEZEL					
WL-19041251	GREEN	12V	20	40	568
WL-19041252	YELLOW	12V	20	40	588
WL-19041253	RED	12V	20	80	625
WL-19041257	BLUE	12V	20	90	466
WL-1904125W	WHITE	12V	20	450	*
WL-19041351	GREEN	24V	20	40	568
WL-19041352	YELLOW	24V	20	40	588
WL-19041353	RED	24V	20	80	625
WL-19041357	BLUE	24V	20	90	466
WL-1904135W	WHITE	24V	20	450	*
WL-19041451	GREEN	28V	20	40	568
WL-19041452	YELLOW	28V	20	40	588
WL-19041453	RED	28V	20	80	625
WL-19041457	BLUE	28V	20	90	466
WL-1904145W	WHITE	28V	20	450	*

*Chromaticity coordinates X=0.31 Y=.032

DIMENSIONAL CHARACTERISTICS



unless otherwise specified, all dimensions are in mm

OPTIONS

Additional options and lens styles available. Please contact Wamco for more information.

NOTES

- Maximum panel thickness 4mm
- Storage temperature
T_{STG}: -25°C – +80°C
- Ambient temperature
T_A: -20°C – +60°C
- DC operation only
- Voltage tolerance
V_{OP}: ±10%
- Electro-optical ratings at
T_A=25°C
- Degree of protection: IP67 in accordance to DIN EN 60529 when using the supplied gasket
- Mounting hole
8 + 0.2mm
- 2.8 x 0.8mm terminals are standard
- Due to production tolerances, slight color variations may be detected within individual consignments
- Supplied with mounting hardware; 1) gasket, 2) spring washer, and 3) M8 nut
- CAUTION: Do not solder directly to terminals

CERTIFICATIONS

RoHS
COMPLIANT



wamco
LIGHTING

P: (714) 545-5560 F: (714) 545-6093

W: WWW.WAMCOINC.COM E: INFO@WAMCOINC.COM

WL-1904XX5X Series Rev 2