

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

19164-0008

Status:

Active

Overview:

Perma-Seal™ Terminals

Description:

Perma-Seal™ Spade Tongue Terminal for 18-22 AWG Wire, Stud Size 10 (M5)



Series

image - Reference only

Documents:

- Drawing (PDF)

Product Specification PS-19902-013 (PDF)
- Product Specification PS-19902-011 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR18689
UL	E32244

General

Product Family	Ring and Spade Terminals
Series	19164
Crimp Quality Equipment	Yes
Mil-Spec	N/A
MolexKits	Yes
Overview	Perma-Seal™ Terminals
Product Name	Perma-Seal™
Type	Spade
UPC	800753112964

Physical

Barrel Type	Closed
Insulation	NiAc™
Material - Plating Mating	Tin
Net Weight	0.907/g
Packaging Type	Bag
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Stud Size	10 (M5)
Wire Insulation Diameter	5.97mm
Wire Size AWG	18, 20, 22
Wire Size mm²	0.38 - 0.96

Material Info

Old Part Number	SA-235-10
-----------------	-----------

Reference - Drawing Numbers

Product Specification	PS-19902-011, PS-19902-013
Sales Drawing	SD-19164-025

EU RoHS

ELV and RoHS
Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

19164Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
PremiumGrade™	0640017400
Hand Crimp Tool	
Power Crimp Tool	0640057400
Head for Terminals	
10-22 AWG Wire	

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION