

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 19203-0005

Status: Active

Overview: High-Temperature Temp Terms Terminals and Splices

Description: Krimptite™ Temp-Term Ring Tongue Terminal for 18 to 22 AWG Wire, Stud Size 1/4" (M6), Mylar Tape Carrier

Documents:

Drawing (PDF)	Product Specification PS-19902-015 (PDF)
Product Specification PS-19902-011 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

UL	E32244
----	--------

General

Product Family	Ring and Spade Terminals
Series	19203
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Overview	High-Temperature Temp Terms Terminals and Splices
Product Name	Krimptite™, Temp-Terms
Type	Ring
UPC	800753049369

Physical

Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Net Weight	0.804/g
Packaging Type	Adhesive Tape on Reel
Stud Size	1/4" (M6)
Wire Size AWG	18, 20, 22
Wire Size mm²	0.25 - 1.50

Material Info

Old Part Number	A-S-122-14T
-----------------	-------------

Reference - Drawing Numbers

Product Specification	PS-19902-011, PS-19902-015
Sales Drawing	SD-19203-036



image - Reference only

Series

EU RoHS

ELV and RoHS
Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product
environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

19203Series

Application Tooling | FAQ

Tooling specifications and manuals are
found by selecting the products below.
Crimp Height Specifications are then
contained in the Application Tooling
Specification document.

Global

Description	Product #
ATP Perishable	0190270026
Tool Kit used in ATP	
Presses that Process	
Product on Tape	
Mini-Mac™	0638854500
Applicator	

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION