This document was generated on 03/03/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 33472-1201

Status: Active

Overview: MX150™ Sealed and Unsealed Connector System

Description: MX150™ Sealed Female Connector, Dual Row, 12 Circuits, Polarization A, without Connector Position Assurance, Black



Series image - Reference only

Documents:

3D Model
Drawing (PDF)
Application Specification AS-33472-100 (PDF)
Application Specification AS-33611-001 (PDF)
RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Housings
Series	33472
Application	Power, Wire-to-Wire
Comments	No Connector Position Assurance (CPA)
More Detailed Tech Information	http://ewcap.uscarteams.org
Overview	MX150™ Sealed and Unsealed Connector System
Product Name	MX150™
UPC	756054494875

Physical

Circuits (maximum)	12
Circuits Detail	12
Color - Resin	Black, Natural
Gender	Female
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Modified Polystyrene Alloy
Net Weight	15.325/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +125°C

Electrical

Current - Maximum per Contact	22A

Material Info

Reference - Drawing Numbers

Application Specification	AS-33472-100, AS-33611-001
Sales Drawing	150-S-012-2-Z01, SD-33472-0001, SD-33472-0002, SD-34345-001

EU RoHS
ELV and RoHS Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, click here

Please visit the Contact Us section for any non-product compliance questions.

Search Parts in this Series
33472Series

Mates With
33482 Male Dual Row Sealed Connector

Use With
33012 MX150™ Female Terminal,
34345-0001 MX150™ Cavity Plug Sealed

This document was generated on 03/03/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION