

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [19067-0110](#)
Status: **Active**
Overview: Solderless Terminals
Description: NylaKrimp™ Funnel Entry Ring Tongue Terminal for 2/0 AWG Wire, Stud Size 1/4" (M6)

Documents:

[Drawing \(PDF\)](#)
[Product Specification PS-19902-011 \(PDF\)](#)
[Product Specification PS-19902-013 \(PDF\)](#)
[Product Specification PS-19902-016 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E32244

General

Product Family Ring and Spade Terminals
Series [19067](#)
Crimp Quality Equipment Yes
Mil-Spec N/A
Overview [Solderless Terminals](#)
Product Name NylaKrimp™
Type Ring
UPC 800753067011

Physical

Barrel Type Closed - Brazed
Flammability 94V-2
Insulation Nylon (PA)
Material - Plating Mating Tin
Net Weight 50.667/g
Packaging Type Bag
Plating min - Mating 2.540µm
Plating min - Termination 2.540µm
Stud Size 1/4" (M6)
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 19.43mm max.
Wire Size AWG 2/0

Material Info

Old Part Number J-985-14

Reference - Drawing Numbers

Product Specification PS-19902-011, PS-19902-013, PS-19902-016
Sales Drawing SD-19067-001




image - Reference only

Series

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[19067Series](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hydraulic Dieless Crimping Tool	0638161700
Manual Putt Pump Hydraulic System, Die set required	0192860117
Die Set (large) for the HHLS Hydraulic Crimper	0192890025