

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

19164-0011

Status:

Active

Overview:

Splices

Description:

Perma-Seal™ 3-Way Connector Assembly for 18-22 AWG Wire

Documents:

Drawing (PDF)

Product Specification PS-19902-011 (PDF)

Product Specification PS-19902-013 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Splices

Series

19164

Crimp Quality Equipment

Yes

Mil-Spec

N/A

Overview

Splices

Product Name

3 Way, Perma-Seal™

UPC

800753112995

Physical

Barrel Type

Closed

Color - Resin

Red

Insulation

NiAc™

Material - Metal

Copper

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Net Weight

1.838/g

Packaging Type

Bag

Temperature Range - Operating

-55°C to +125°C

Termination Interface: Style

Crimp or Compression

Wire Insulation Diameter

5.46mm max.

Wire Size AWG

18, 20, 22

Wire Size mm²

0.38 - 0.96

Electrical

Voltage - Maximum

600V

Material Info

Old Part Number

SA-2YCX

Reference - Drawing Numbers

Product Specification

PS-19902-011, PS-19902-013

Sales Drawing

SD-19164-051, SD-19204-001



Series

image - Reference only

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

19164Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
PremiumGrade™	0640017400
Hand Crimp Tool	
Power Crimp Tool	0640057400
Head for Terminals	
10-22 AWG Wire	

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION