

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

84729-0003

Status:

Active

Overview:

Sealed Industrial USB Solutions

Description:

Sealed Industrial USB 2.0 Type A Plug-to-USB 2.0 Type A Receptacle, 28 AWG, 0.152M Length

Documents:

Drawing (PDF)

Product Specification PS-84727-002 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Assembly Configuration

Comments

Connector to Connector

Overview

Product Name

UPC

Cable Assemblies

84729

Dual Ended Connectors

Fully shielded for EMI/RFI protection

Type A Recept-to-Type A Plug

Sealed Industrial USB Solutions

Industrial USB

822348831999

Physical

Cable Length

Circuits (Loaded)

Color - Resin

Gender

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Packaging Type

Plating min - Mating

Plating min - Termination

Single Ended

Waterproof / Dustproof

Waterproof / Dustproof Type

Wire Size AWG

Wire/Cable Type

0.152m

4

Black

Female-Male

Phosphor Bronze

Gold

Gold

PBT

Bag

0.762µm

0.762µm

No

Yes

IP67, NEMA 6P

28

USB

Electrical

Current - Maximum per Contact

Impedance

Shield Type

Shielded

Voltage - Maximum

1A

90#

Full Shield

Yes

30V AC (RMS)

Material Info

Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-84727-002

SD-84729-006



EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

84729Series

Mates With

Industry Standard Bayonet Locking USB Type A Plug and Industry Standard USB Type A Receptacle