



--



(1P×26AWG)*4+AL	CAT7
4P	
7/0.16mm	
TA	
e	
FM-PE+SKIN	
1.05±0.03mm	
E318309 (UL) AWM 2835	75℃ 30V SSTP CAT7 4PAIRS
TIA/EIA 568B 26AWG	

- 1.ELECTRICAL TEST: 100% OPEN,SHORT & MISS WIRE TEST.
- 2.CONDUCTOR RESISTANCE: 5 OHMS MAX. INSULATOR RESISTANCE:5M OHMS MIN.
- 3.HI-POT:DC 300V 0.01sec.
4. ALL MATERIAL FIT ROHS STANDARD(INCLUDE ALL PACKING OR OTHER MATERIAL).
- 5.PRINTING WORD OF CABLE:E318309 (UL) AWM 2835 75°C 30V SSTP CAT7 4PAIRS TIA/EIA 568B 26AWG



REVISION	NOTES	DATE			MAT'L:	FINISH:
A		21/11/11				
			DRAWN BY	DK	TITLE : CAT 7 round	PART NO:
			DATE	21/11/11		
			UNITS	METRIC mm		