



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

## Protect It! 1-Outlet Portable Surge Protector, Direct Plug-In, 600 Joules, Tel/Modem Protection

MODEL NUMBER: **TRAVELCUBE**



### Description

The TRAVELCUBE is designed for convenient portable and economical surge protection. Small and powerful, the TRAVELCUBE features 540 joules and carries \$10K of insurance as well as a . Throw it in a briefcase or purse and have quality surge protection wherever you need it — hotel room, dorm, client office — anywhere!

### Features

- Portable wall-mount cube stores easily in any bag or briefcase
- 1 NEMA5-15R AC outlet
- 540 joules of protection shields equipment from harmful surges, spikes and line noise
- Diagnostic LED displays protection status
- Built-in tel/modem surge protection
- Bonus 6-ft. phone cord included
- UL 1449 rated 3rd Edition
- \$10,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

## Specifications

OVERVIEW	
Style	Direct Plug-in
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(1) 5-15R

### Highlights

- 1 AC outlet
- Direct plug-in design
- Built-in tel/modem surge protection
- 540 joule rating
- Diagnostic LED displays protection status
- \$10,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

### Applications

- Ideal for use with laptops, fax machines, electronic notepads, personal organizers and other portable electronic devices

### Package Includes

- TRAVELCUBE surge suppressor
- Bonus 6-ft. telephone cord



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Output (Watts)	1800
Circuit Breaker (amps)	15
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-15P input plug
Input Cord Length (ft.)	0
Input Cord Length Details	Direct plug-in
Voltage Compatibility (VAC)	120
Maximum Surge Amps	36000
<b>LEDS ALARMS &amp; SWITCHES</b>	
Diagnostic LEDs	Built-in LED confirms suppressor "protection present" (red) status
<b>SURGE / NOISE SUPPRESSION</b>	
AC Suppression Joule Rating	540
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	500V
EMI / RFI Filtering	Up to 20dB
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection	Yes
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	2.83 x 5.12 x 6.50
Shipping Dimensions (hwd / cm)	7.19 x 13.00 x 16.51
Shipping Weight (lbs.)	.42
Shipping Weight (kg)	0.19
Unit Dimensions (hwd / in.)	1.49 x 2.16 x 3.07
Unit Dimensions (hwd / cm)	3.78 x 5.49 x 7.80



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Unit Weight (lbs.)	.17
Unit Weight (kg)	0.08
Material of Construction	Plastic
Form Factors Supported	Direct plug in suppressor supports wall-mounting directly into AC receptacle
<b>CERTIFICATIONS</b>	
UL1449 3rd Edition (AC Suppression)	UL1449 3RD EDITION
Approvals	Exceeds IEEE 587 category A&B specifications
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$10,000 Ultimate Lifetime Insurance

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.