


# EcoClassic A-shape

## EcoClassic 42W E27 240V A55 CL 1CT

Philips EcoClassic light bulbs offer the classical shapes you are used to, but with better energy efficiency. This new 'classic' gives high-quality light, is dimmable and starts immediately.

## Product data

### General Characteristics

| | |
|---|---|
| Cap-Base | ES [ES] |
| Bulb | A55 [A 55mm] |
| Bulb Finish | Clear |
| Burning Position | any [Any/Universal] |
| Nominal Lifetime | 2000 hr |
| Rated Lifetime | 2000 hr |
| Rated Lifetime (years) | 2 an |

### Light Technical Characteristics

| | |
|---|---|
| Colour Rendering Index | 100 Ra8 |
| Colour Temperature | 2800 K |
| Colour Temperature Technical | 2800 K |
| Lamp Luminous Flux | 630 Lm |
| Rated Luminous Flux | 630 Lm |
| Lamp Luminous Efficacy | 15.0 Lm/W |
| LLMF - end nominal lifetime | 80 (min) % |

### Electrical Characteristics

| | |
|---|---|
| Rated Wattage | 42.0 W |
| Lamp Wattage | 42 W |
| Technical Lamp Power | 42 W |
| Power Factor | 1 - |
| Voltage | 240 V |
| Lamp Current | 0.18 A |
| Dimmable | yes |
| Wattage Equivalent | 55 W |
| Starting Time | 0.0 s |
| Warm-up Time to 60% Light Outp | instant full light |

### Environmental Characteristics

| | |
|---|---|
| Energy Efficiency Label (EEL) | D |
| Energy consumption kWh/1000h | 42 kWh |

### Measuring Conditions

| | |
|---|---|
| Switching cycle | 8000X |

### Luminaire Design Requirements

| | |
|---|---|
| Cap-Base Temperature | 130 (max) C |

### Product Dimensions

| | |
|---|---|
| Overall Length C | 97 (max) mm |
| Diameter D | 56 (max) mm |

### Product Data


| | |
|---|---|
| Order code | 251791 25 |
| Full product code | 872790025179125 |
| Full product name | EcoClassic 42W E27 240V A55 CL 1CT |
| Order product name | EcoClassic 42W E27 240V A55 CL 1CT/10 |
| Pieces per pack | 1 |
| Packing configuration | 10 |
| Packs per outerbox | 10 |
| Bar code on pack - EAN1 | 8727900251791 |

PHILIPS

# EcoClassic A-shape

| | | | |
|---|---|---|---|
| Bar code on outerbox - EAN3 | 8727900660579 | Net weight per piece | 26.100 gr |
| Logistic code(s) - 12NC | 925693045501 | | |

## Dimensional drawing







E27

### EcoClassic 42W E27 240V A55 CL 1CT

| Product | C (Max) | D (Max) |
|---|---|---|
| EcoCl30 42W E27 240V A55 CL | 97 | 56 |

© 2014 Koninklijke Philips N.V. (Royal Philips)
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

**www.philips.com/lighting**

2014, April 17
data subject to change