

EAO – Your Expert Partner for Human Machine Interfaces

82-4151.2114 - Illuminated pushbutton 16 mm stainless-steel, maintain

82-4151.2114 - Illuminated pushbutton 16 mm stainless-steel, maintain



Attention: The preview is based on a sample product. This can differ from your current configuration.

Mounting

Design	flush
Mounting cut-out	Ø 16 mm

Front

Front shape	round
Front ring shape	flush
Front dimension	Ø 18 mm

Other Attributes

Operating voltage	24 V AC/DC
Weight	0.018 kg
Operation current	10 mA

Operating-/Indication part

Lens optics	opaque
Lens material	Stainless steel
Lens profile	flat
Lens illumination	illuminative
Lens colour	Stainless steel

IP-Rating

Front protection	IP 67
------------------	-------

Connection Method

Terminal	Solder 2.8 x 0.5 mm
----------	---------------------

Actuator

Switching action	Maintained
------------------	------------

Switching element

Switching current	5 A
Contact material	Silver
Contacts	1 C
Switching system	Snap-action switching element
Switching voltage	250 V AC

Illumination

Illumination	Ring with red LED
--------------	-------------------


Function

Illuminated pushbutton	
------------------------	--


EAO – Your Expert Partner for Human Machine Interfaces

82-4151.2114 - Illuminated pushbutton 16 mm stainless-steel, maintain


Dimensions




Mounting cut-outs



Wiring diagram



Component layout



Legend

Switching action: C = Maintained

Contacts: C = Changeover