

5

4

3

2

1

受控 CONTROLLED DOCUMENT

编号 P/N	30-1008KUL-CUST	版本 Rev	01	日期 Rel'd Date	SEP 17,09
-----------	-----------------	-----------	----	------------------	-----------

Description: 8Cond MOD Coupler Keyed,Wire S
 Part No: 30-1008KUL
 Application: N/A
 Crimp Tool: N/A
 Impedance: N/A
 Frequency Range: N/A
 Material: Cover PVC UL
 Wire 1007#26AWG UL
 Pin Brass,Gold Plated
 Gilt FU"
 RoHS Compliance: Yes
 Technical Detail: N/A

DRAWING NO.
30-1008KUL-CUST

REVISIONS

01	OFFICIAL RELEASE				2009.09.1
	08-17-09	Y	U	T	H

Betty 610:5870
+0800©

D

D

C


C

B

B

A

A

**DIM OUTLINE**

PIN ASSIGNMENT

1	1	WHITE
2	2	BROWN
3	3	YELLOW
4	4	GREEN
5	5	RED
6	6	BLACK
7	7	ORANGE
8	8	BLUE

CUSTOMER COPY

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY BETTY.YU	DATE 08-17-09
DECIMALS	mm	CHECKED BY BETTY.YU	DATE 08-17-09
X	± 0.5	APPROVED BY THOMAS	DATE 08-17-09
X.X	± 0.3	U/M	mm
X.XX	± 0.1		
ANGLES	± 0.5°		


cinch
 CONNECTIVITY SOLUTIONS
 a bel group
TITLE
8COND MOD COUPLER
KEYED,WIRE SSHEET
1 OF 1DRAWING NO.
30-1008KULSIZE
ATHIS DRAWING WAS PRODUCED BY COMPUTER,
DO NOT SCALE DRAWING OR UPDATE MANUALLY.

5

4

3

2

1