

## 4 Port Black USB KVM Switch Kit with Cables and Audio

StarTech ID: SV411KUSB



The SV411KUSB 4 Port USB KVM Switch Kit with Audio and Cables lets you control up to four USB-enabled computers using a single keyboard, mouse and VGA monitor and offers both hotkey and top panel push-button operation for simple switching between connected computers.

Designed to integrate seamlessly into any environment, the USB KVM switch offers a small footprint design (roughly the size of a deck of playing cards) and draws power from the connected computers, so it doesn't require an external power supply.

A suitable solution for virtually any application, the USB KVM switch supports video resolutions of up to 2048 x 1536 as well as audio switching. The USB KVM switch includes four, 4ft 4-in-1 VGA and USB Host Cables, providing everything needed for quick installation to provide a complete, out-of-the-box KVM solution.

Delivering dependable and convenient control of multiple computers from a single peripheral station, the KVM switch is backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Applications

- Control 4 USB-enabled computers using a single keyboard, mouse, and VGA monitor
- Applicable for call centers, help desks, education environments, home gamers, video editing, and PC enthusiasts
- Great for PC test/burn-in computer control saving the desk space required for multiple monitors, keyboards and mice
- Multiple system control for single user workstations, increasing user productivity in the office

## Features

- Cables (4 ft.) included
- Includes audio support for a complete switching solution
- Maximum resolution: 2048 x 1536
- Switching type: Hotkey, push-button

Technical Specifications

Warranty	2 Years
Audio	Yes
Cables Included	Yes
Daisy-Chain	No
KVM Ports	4
Multi-Monitor	No
PC Interface	USB
PC Video Type	VGA
Rack-Mountable	No
Console Interface(s)	1 - VGA (15 pin; High Density D-Sub) Female
Console Interface(s)	2 - 3.5 mm Mini-Jack (3 Position) Female
Console Interface(s)	2 - USB A (4 pin) Female
Host Connectors	4 - VGA (15 pin; High Density D-Sub) Female
Host Connectors	8 - 3.5 mm Mini-Jack (3 Position) Female
DVI Support	No
IP Control	No
Maximum Analog Resolutions	2048 x 1536 pixels
Maximum Number of Users	1
OS Compatibility	OS independent; No software or drivers required
Cable Length	1.2 m [4 ft]
Color	Black
Enclosure Type	Plastic
Product Depth	61 mm [2.4 in]
Product Height	25 mm [1 in]
Product Weight	110 g [3.9 oz]
Product Width	95 mm [3.7 in]
Power Source	USB-Powered
Shipping (Package) Weight	1.6 kg [3.4 lb]
Included in Package	1 - 4 Port KVM Switch
Included in Package	4 - 4ft. Audio Cable (3.5mm speaker/mic)
Included in Package	4 - 4ft. VGA USB KVM Cable
Included in Package	1 - Driver CD
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

