



MATERIALS:

Body – Gold Plated Brass, Jacks – Gold Plated Beryllium Copper
 Insulator – Nylon

Maximum Panel thickness: .25" (6.4)

Standard Colors: -0 Black; -2 Red

RATING:

5 Amps

Hands free testing to 1500 VMRS max.

Temperature: -50°C to 105°C