
3.5 (88.90)
.24 (6.05)
.25
(6.35)
3.0 (76.20)
M0
M1
M2
M3
50-PIN
STRAIGHT
HEADER
CONNECTOR
REMOVABLE JUMPER
CONNNECTS GND
TO PLATED HOLE
FOR GROUNDING
3.8
(96.52)
4.3
(108.46)
3.15A FUSE
PIN 1
FIELD WIRING
TERMINAL STRIP
STANDOFF I.D. 0.15
(3.81) DIA. (4 PLACES)
CLEARANCE FOR #6 SCREW
NOTE: MAXIMUM
TERMINAL SCREW
TORQUE NOT TO
EXCEED 5 IN-LBS.


LOGIC SUPPLY
TERMINAL STRIP
TOP ROW: + LOGIC SUPPLY
BOTTOM ROW: GND
3.4
(85.93)
MAX
.75
(19.05)
REF


LOGIC SUPPLY
TERMINAL STRIP
1 2 3 4 5 6 7 8 9 10 11 12 13 14 15 16
FIELD
WIRING
TERMINAL
STRIP
5A FUSE
0 1 2 3 4 5 6 7
MODULE
POSITION
N/C
26-PIN EDGE
CONNECTOR
FOR LOGIC
SIGNALS
3.3K
50-PIN EDGE
OR HEADER
CONNECTOR
FOR LOGIC
SIGNALS
USER INSTALLABLE JUMPERS
FOR +VCC (3 PLACES)





Part Number	I/O	Description	UL	CSA	Style