

Soldering / Tining machines

ROLLER TINNING MACHINES



Entirely constructed in stainless steel, our range of roller tinning machines is suitable for working in a laboratory or for low volume small production.

Heavy-duty and reliable, a well-maintained machine will last for more than 10 years.

Manual tinning machines

Access and removal of rollers, and disengagement of the pressure roller, is in a single operation. Thermostat on all models.

Motor protection to prevent starting when the tin is solid.

Model 1

Tinning width : 220 mm

Solder bath capacity : 6 kg

Electrical supply : 1000 W

Dimensions (L x I x H) : 440 x 260 x 210 mm

Weight without solder : 22 kg

Model 2

Tinning width : 420 mm

Solder bath capacity : 11 kg

Electrical supply : 2000 W

Dimensions (L x I x H) : 640 x 260 x 210 mm

Weight without solder : 32 kg

Model 1	DP 63
Model 2	EP 64

Automatic tinning machines

Tinning width : 420 mm

Solder bath capacity : 11 kg

Electrical supply : 2000 W

Adjustable speed

Weight without solder : 35 kgs

Item code	EP 65
-----------	-------