



7-1618387-1 Product Details



Contactors

LEV200A5ANA=RELAY, SPST-NO

7-1618387-1 (LEV200A5ANA)

TE Internal Number: 7-1618387-1

Product Highlights

- Contactor Type = Sealed
- LEV200 Series
- DC Actuating System
- 1 Poles
- Contact - Arrangement = 1 Form X, SPST-NO-DM

Please Note:

Use the Product Drawing for all design activity

Product Type Features

Contactor Type Sealed

Terminal Configuration 10-32 Stud

Electrical Characteristics

Actuating System DC

Contact Rating 500A

Coil - Rated Voltage (VDC) 24

Coil Voltage, Max. (VDC) 24

Termination Features

Coil Termination Wire

Dimensions

Coil Wire Length (mm [in]) 390 [15.3]

Body Features

Torque 80-100 in-lbs

Mount Type Bottom Mount

Contact Features

Number of Poles 1

Configuration Features

Contact - Arrangement 1 Form X, SPST-NO-DM

Auxiliary Switch Contact Arrangement None

Industry Standards

RoHS/ELV Compliance RoHS compliant, ELV compliant

Lead Free Solder Processes Not relevant for lead free process

RoHS/ELV Compliance History Always was RoHS compliant

Packaging Features

Packaging Method Individual

Other

Series LEV200

Brand Kilovac