

LABFACILITY

TEMPERATURE & PROCESS TECHNOLOGY

Miniature Quick Wire Panel Mount Socket with Stainless Steel Bracket



'IEC Colour coded'

manufacturer of both temperature sensors and

We are the largest UK

About Labfacility Formed in 1971, Labfacility specialize in the field of **Temperature and Process**

Measurement.

- thermocouple connectors
- Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

Contact Details

Email sales@labfacility.com

www.labfacility.com

- Miniature size sockets supplied with stainless steel brackets
- Available in Thermocouple types K, J, T, E, N, R/S, B
- For Types K, J, T, E & N contacts are made from true Thermocouple alloys
- Colour coded in accordance with IEC specification
- Maximum continuous operating temperature 220 deg°C

T/C Type	Colour Code (IEC)	+Positive Contact (alloy type)	-Negative Contact (alloy type)	Part Code	Farnell Order Code
K	Green	+Nickel Chromium	-Nickel Alloy	IM-K-SSPFQ	859-8304
В	Grey	+Copper	-Copper	IM-B-SSPFQ	234-7044
Ε	Violet	+Nickel Chromium	-Copper Nickel	IM-E-SSPFQ	234-7045
J	Black	+Iron	-Copper Nickel	IM-J-SSPFQ	234-7046
N	Pink	+Nickel/Chro/Silicon	-Nickel Silicon	IM-N-SSPFQ	234-7047
R/S	Orange	+Copper	-Copper Alloy	IM-R/S-SSPFQ	234-7048
T	Brown	+Copper	-Copper Nickel	IM-T-SSPFQ	234-7049

