




Thermocouple Extension Cable PFA Insulated Flat Pair Thermocouple types K, J, T & N



- ◆ PFA Teflon® insulated flat pair
- ◆ Single pair of PFA insulated conductors, laid flat with PFA jacket
- ◆ Good mechanical strength and flexibility, resistant to oils, acids and other adverse fluids
- ◆ 25, 50 & 100 metre reel lengths
- ◆ Tolerance Class 1 for optimum accuracy
- ◆ Insulation rating -75°C to 260°C
- ◆ Colour code (cores & jacket) to IEC-584-3

T/C Type	Conductors	mm ²	Cores	Jacket	Reel Length	Manufacturers Part No.	Farnell order code
K	1/0.3mm	0.072	+Green/-White	Green	25m	WK-356-D-25M	208-1284
K	7/0.2mm	0.219	+Green/-White	Green	25m	XS-751-D-25M	208-1285
K	7/0.2mm	0.219	+Green/-White	Green	50m	XS-751-D-50M	208-1286
K	7/0.2mm	0.219	+Green/-White	Green	100m	XS-751-D-100M	208-1287
J	7/0.2mm	0.219	+Black/-White	Black	25m	WJ-248-D-25M	208-1281
J	7/0.2mm	0.219	+Black/-White	Black	50m	WJ-248-D-50M	208-1282
T	1/0.3mm	0.072	+Brown/-White	Brown	25m	WT-203-D-25M	208-1288
T	7/0.2mm	0.219	+Brown/-White	Brown	25m	WT-305-D-25M	208-1289
T	7/0.2mm	0.219	+Brown/-White	Brown	50m	WT-305-D-50M	208-1290
T	7/0.2mm	0.219	+Brown/-White	Brown	100m	WT-305-D-100M	208-1291
N	7/0.2mm	0.219	+Pink/-White	Pink	25m	WN-121-D-25M	208-1292

About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors

Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

Contact Details

Email
sales@labfacility.com

Website
www.labfacility.com