

Black Box Products

Industrial > Cabling & Infrastructure

Bulk Extended-Distance/Quiet Cable—Industrial Environment, PVC Jacket, 7 Conductors (3 1/2 Pairs), 1000-ft. (304.8-m)

Send RS-232 data up to 500 feet in noisy environments.

EMN07A-1000

Product Highlights

- Low capacitance, braided foil shield.
- 24 AWG stranded construction
- Guaranteed for life!



Cable Type	Twisted pair, PVC jacket
Capacitance	12 pF/ft. \pm 2 pF/ft.
Conductor Gauge	24 AWG (7 x 32 AWG) stranded
Resistance	25 ohms/1000 ft.
Shield	One foil and one copper braid