

NetCommander 16-Port Cat5 KVM Switch 1U Rack-Mount

MODEL NUMBER: **B072-016-1**



Description

Tripp Lite's 16-Port NetCommander 1U Rackmount Cat5 KVM Switch, is the next generation of our cost-effective, feature rich, KVM switches. It's sleek, 1U design and compact size, features RJ45 connection ports that utilize inexpensive Cat5 patch cables, reducing the amount of cable clutter normally found with traditional KVM cabling. Easily switch between CPU's with Push Buttons, Hot-Key commands, or built-in On Screen Display (OSD) menu function. Cascadability allows connection to up to 256 computers. Compatible with PS/2 and USB computers, VGA, SVGA, or XGA monitors, as well as all major operating systems. Constructed of heavy-duty steel housing.

Features

- Powerful control 1-256 computers from one KVM console
- Extend distance between computer and switch up to 30 meters/100ft
- Rack mountable sleek, 1U space saving KVM switches
- Innovative CAT5 technology eliminate cable clutter at the rack
- Multi-layer security protects your corporate data
- Easy server management choice of On Screen Display, Hot-key, or push button control
- Multi-platform - PS/2, SUN, and USB support
- Easily add IP functionality with Tripp Lite Model [B051-000](#)
- Add Tripp Lite Model [B021-000-17](#) for space saving, in-the-rack, LCD, Keyboard and Mouse.
- Compact Size: 17"W x 5"D x 1.75"H
- Video Resolution: 1600x1200@75Hz
- Internal Power Supply
- Compatible with all major operating systems
- Constructed of heavy-duty steel housing

Specifications

Highlights

- 16 RJ45 Ports utilize inexpensive Cat5 patch cables
- Expandable - control up to 256 servers from a single station
- 3 ways to switch between servers
 - Push buttons, Hot-Keys, On Screen Display menu
- Supports PS2 and USB CPUs
- 1U Rackmountable - includes mounting hardware
- Compatible with all major operating systems

System Requirements

- Computers: The Tripp Lite [B078-101-PS2](#), or [B078-101-USB](#) Server Interface Module must be used to connect a computer/server
- Compatible with all major operating systems

Package Includes

- 16-Port NetCommander 1U Rackmount Cat5 KVM Switch
- 6-ft Power Cord
- 6-ft Serial Cable
- Rackmount Bracket kit



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

General Info	
RoHS	Y
OVERVIEW	
Users	1
Console	No
Port Control	Push Buttons, Hotkeys, OSD
Max CPU	256
PC/Server Connections	VGA; USB; PS/2
Cat5 KVM Switch	Yes
IP Remote Access	Yes
Style	1U Rackmount
PHYSICAL	
Color	Black
LCD Monitor (in.)	Not Applicable
LCD Monitor (cm)	Not Applicable
ENVIRONMENTAL	
BTUs	27.296
CONNECTIONS	
Connector A	HD15 (FEMALE)
Connector B	MINI DIN-6 (FEMALE) (X2)
Ports	16
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.