



T-1 1/2 Wedge Base





Part Number	Design Voltage	Amps	MSCP	Life Hours	Filament Type
6502	4.0	.250	.200	1,000	C-2V
1103	6.0	.030	.024	1,000	C-2R
1104	6.0	.080	.070	5,000	C-2V
3105	6.0	.167	.300	5,000	C-2R
6516	6.0	.178	.720	1,000	C-2R
6521	6.0	.167	.480	1,000	C-2R
6522	6.0	.030	.040	1,000	C-2V
6515	7.0	.035	.040	1,000	C-2V
1107	12.0	.030	.080	1,000	C-2V
1108	12.0	.080	.240	5,000	C-2R
286	13.5	.090	.570	200	C-2V
1111	24.0	.040	.240	5,000	C-2F
3110	24.0	.030	.100	5,000	C-2F

T-1 3/4 Wire Terminal



Part Number	Design Voltage	Amps	MSCP	Life Hours	Filament Type
2184	1.30	.050	.020	30	S-2
1728	1.35	.060	.010	500	C-6
2119	2.00	.060	.001	5,000	C-2R
1783	2.50	.200	.220	500	C-2R
2169	2.50	.350	.200	10,000	C-2R
2264	2.50	.400	.280	5,000	C-2R
1738	2.70	.060	.040	6,000	C-2R
2129	3.00	.300	.340	1,500	C-2R
2156	3.00	.030	.020	1,800	C-6
2158	3.00	.015	.004	10,000	C-6
8847	3.00	.350	.300	10,000	C-2R
2171	4.50	.120	.040	25,000	C-2F
2200	5.00	.060	.050	25,000	C-2R
2203	5.00	.115	.150	40,000	C-2R
3151	5.00	.060	.150	5,000	C-2R
3626	5.00	.060	.050	25,000	C-2R
3627	5.00	.220	.600	30,000	C-2R
3628	5.00	.220	.600	30,000	C-2R
3950	5.00	.017	.018	2,000	C-2R
8784	5.00	.190	.450	1,000	C-2R
8805	5.00	.060	.030	60,000	C-2R
1730	6.00	.040	.030	10,000	C-2V
1784	6.00	.200	.600	1,000	C-2R
2191	6.00	.036	.010	40,000	C-2V
8664	6.00	.200	.100	50,000	C-2F

T-1 3/4 Wire Terminal (standard)



Part Number	Design Voltage	Amps	MSCP	Life Hours	Filament Type
1739	6.30	.070	.230	1,000	C-2R
2037	6.30	.200	.400	20,000	C-2R
2039	6.30	.075	.230	1,000	C-2R
2112	6.30	.200	.550	5,000	C-2R
2179	6.30	.040	.030	20,000	C-2V
2180	6.30	.040	.020	20,000	C-2V
2181	6.30	.200	.400	20,000	C-2F
8350	6.30	.150	.450	3,000	C-2R
2178	8.00	.085	.150	25,000	C-2F
1869	10.00	.014	.002	50,000	C-2F
2107	10.00	.040	.080	5,000	C-2F
2149	10.00	.014	.002	50,000	C-2F
8946	11.00	.022	.030	10,000	C-2F
2174	12.00	.040	.100	10,000	C-2F
1705	14.00	.080	.500	1,500	C-2F
2162	14.00	.100	.500	10,000	C-2F
2182	14.00	.080	.300	40,000	C-2F
2382	14.00	.080	.300	40,000	C-2F
2102	18.00	.040	.150	10,000	C-2F
8425	22.00	.040	.300	2,000	C-2F
2041	24.00	.060	.500	5,000	C-2F
2176	24.00	.050	.500	1,000	C-2F
476	28.00	.060	.340	25,000	C-2F
1749	28.00	.060	.340	25,000	C-2F
1762	28.00	.040	.340	4,000	C-2F
1764	28.00	.040	.340	4,000	C-2F
2185	28.00	.040	.150	10,000	C-2F
2187	28.00	.040	.300	7,000	C-2F
2287	28.00	.040	.300	7,000	C-2F
2370	28.00	.050	.700	1,000	C-2F
6033	28.00	.024	.150	4,000	CC-2F
8361	28.00	.065	.650	5,000	C-2F
8461	28.00	.050	.500	5,000	C-2F
1918	32.00	.040	.300	7,000	C-2F
6748	48.00	.025	.200	5,000	CC-2F