



Prokit's Industries CO., LTD.

5F, No.7, Lane 130,
Ming-Chung Rd., Hsin-Tien Dist,
New Taipei City, Taiwan, R.O.C. Post code: 23114
Tel: 886-2-2218-3233; Fax: 886-2-2218-2722

<http://www.prokits.com.tw> Email: sales-c@mail.prokits.com.tw

PRODUCT SPECIFICATION

Item #	Farnell Item #	Description	MOQ	Carton Quantity	N.W	G.W	CUFT
PK-15307BM-40	1666222	Electronic Tool Kit (220V, Metric)	2 set	2 set	15 kgs	17 kgs	2.44



*** Picture for reference only. All specifications are subject to change by supplier. ***

Spec.

Item No.	Description
1PK-067DS	Dual Color Side Cutting Plier 165 mm
1PK-709DS	Dual Color Long Nose Plier
1PK-051DS	Dual Color Lineman's Plier 205 mm
PM-736	Long Nose Plier 135 mm
PM-737	Diagonal Cutting Plier 113 mm
9SD-201A	PRO-SOFT Slotted Screwdriver (3.0 x 75 mm)
9SD-201B	PRO-SOFT Phillips Screwdriver (#0 x 75 mm)
9SD-202A	PRO-SOFT Slotted Screwdriver (5.0 x 75 mm)
9SD-202B	PRO-SOFT Phillips Screwdriver (#1 x 75 mm)
9SD-207A	PRO-SOFT Slotted Screwdriver (6.0 x 100 mm)
9SD-207B	PRO-SOFT Phillips Screwdriver (#2 x 100 mm)
9SD-220A	PRO-SOFT Slotted Screwdriver (6.0 x 40 mm)
9SD-220B	PRO-SOFT Phillips Screwdriver (#2 x 40 mm)
9SD-217B	PRO-SOFT Phillips Screwdriver (#2 x 250 mm)
SD-081-S3	PRO-SOFT Precision Slotted Screwdriver 2.0 x 50 mm
SD-081-S6	PRO-SOFT Precision Slotted Screwdriver 2.4 x 75 mm
SD-081-S7	PRO-SOFT Precision Slotted Screwdriver 3.0 x 100 mm
SD-081-P2	PRO-SOFT Precision Phillips Screwdriver #00 x 50 mm
SD-081-P5	PRO-SOFT Precision Phillips Screwdriver #0 x 75 mm
SD-081-P7	PRO-SOFT Precision Phillips Screwdriver #1 x 150 mm

8PK-S120NB-40	40W Soldering Iron with EU plug, CE & RoHS compliance (480°C±10%)
SN-310G	Solder Core (Sn 99.3%, Cu 0.7%)
DP-366P	Desoldering Pump
DP-3615	Solder Aid Tools
SH-1025	Soldering Tip Cleaner
MT-1210	3-1/2 Compact Digital Multimeter
PN-086	Slip Joint Plier 154 mm
1PK-H026	Adjustable Wrench (150mm)
HW-609B	10 PCS Electronic Combination Wrenches (Metric)
CP-108	Wire Stripper Cutter
HW-002B	7 PCS Hex Key Set (Metric)
8PK-605A	5 PCS Needle File Set
SB-1912	Utility Component Storage Box
SR-330	All Purpose Snip
8PK-108T	Reverse Action Tweezer
8PK-125T	Fine Tip Straight Tweezer
PD-374	Hobby Vise (Jaw Opening: 40 mm, Width: 60 mm)
9S004	Heat Sink
908-609	IC Extractor
DK-2039	Utility Knife with 3 Spare Blades
DK-2040	Measuring Tape (L=3M / 10FT)
MS-035	Flux Bottle (2 PCS / PACK)

MS-153C	Blow Brush (Φ56 mm)
9PK-730N	Aluminum Frame Tool Case (458 x 330 x 150 mm)
9PK-15307-P	Pallet for PK-15307
9PK-15307-TP	Top Pallet for PK-15307

Individual packing: Color box

Measurement of Tool Case (458 x 330 x 150 mm), Carton (480 x 360 x 400 mm)

~ THE END ~