

# Molex Kit 76650-0043



<b>Kit Part Number:</b>	<b>76650-0043</b>
<b>Category:</b>	Solderless Terminals
<b>Solution:</b>	Maintenance, Repair and Operation
<b>Molex Connector Family:</b>	Solderless Terminals
<b>Description:</b>	Solderless Terminal Kit
<b>Number of Pieces:</b>	491 Pieces
<b>ROHS:</b>	Yes
<b>Lead-Free:</b>	Yes

## Product Highlights

Quick disconnects allow for quickly connecting or disconnecting a terminal. The front end of the terminal has a female-type receptacle which allows the terminal to slide onto and off of a male blade. Spades have the open tongue end used for rapid insertion on the mounting screw. The spade is usually used on free standing studs. Closed-end connectors are used in a variety of situations to "pigtail" or tie together 2 or more wires. Butt Splices allow two stripped wires to be inserted into each end and "butt" in the center, with the crimp securing both wires together.

## Features and Benefits

- Color-coded insulator allows easy identification of terminal size and wire gauge.
- A wire stop stamped into the crimp barrel prevents insertion of over-stripped wires.
- Terminals funnel entrance is designed for increased crimping rates by speeding wire delivery into the crimp section and eliminating wire strand fold back.
- The spades open tongue end is for rapid insertion on the mounting screw / stud
- The basic ring tongue type is the safest and most reliable because it cannot be disconnected unless the screw is completely removed.

## **Applications**

- MRO (Maintenance Repair and Operations)
- Consumer Applications
- Power Applications
- Motor Applications
- Powertrains
- Transportation
- Construction / Mining
- Energy / Power
- Production Equipment
- Instrumentation
- Environmental Equipment and Controls
- Blower Motors

## **Specifications**

<b>Insulation</b>	PVC, Nylon
<b>Insulation Type</b>	PVC Insulated, Nylon
<b>Mounting Style</b>	Non-Mounted
<b>Orientation</b>	Assorted Quick Disconnect Terminals
<b>Product/Type</b>	Assorted Terminals
<b>Stud/Tab Size</b>	# 6, .250" (6.35mm), 1/4" (6.35mm), 3/8" (9.52mm), 3/8"
<b>Tool</b>	Yes
<b>Wire Gauge (AWG)</b>	12-10, 16-14 , 22-18, 22-14

## Kit Contents

<b>Molex P/N</b>	<b>Qty In Kit</b>	<b>Description</b>
<a href="#">19004-0005</a>	25	Fully Insulated 6.35mm (.250") Male Quick Disconnect Terminal, 16-14 AWG
<a href="#">19005-0005</a>	25	Fully Insulated 6.35mm (.250") Female Quick Disconnect Terminal, 16-14 AWG
<a href="#">19017-0037</a>	25	Insulated 6.35mm (.250") Female Quick Disconnect Terminal, 16-14 AWG
<a href="#">19023-0012</a>	25	Insulated 6.35mm (.250") Male Quick Disconnect Terminal, 16-14 AWG
<a href="#">19054-0033</a>	25	Insulated #6 Ring Tongue Terminal, 22-18 AWG
<a href="#">19054-0081</a>	25	Insulated #6 Ring Tongue Terminal, 16-14 AWG
<a href="#">19054-0086</a>	25	Insulated 1/4" Ring Tongue Terminal, 16-14 AWG
<a href="#">19054-0113</a>	25	Insulated #10 Ring Tongue Terminal, 16-14 AWG
<a href="#">19070-0123</a>	25	Insulated #10 Ring Tongue Terminal, 12-10 AWG
<a href="#">19070-0153</a>	25	Insulated 3/8" Ring Tongue Terminal, 12-10 AWG
<a href="#">19142-0003</a>	25	Insulated #6 Spade Terminal, 22-18 AWG
<a href="#">19142-0029</a>	25	Insulated #6 Spade Terminal, 16-14 AWG
<a href="#">19142-0032</a>	25	Insulated #10 Spade Terminal, 16-14 AWG
<a href="#">19144-0042</a>	25	Insulated #10 Spade Terminal, 12-10 AWG
<a href="#">19154-0004</a>	25	Insulated Butt Splice Connector, 22-18 AWG
<a href="#">19154-0015</a>	25	Insulated Butt Splice Connector, 16-14 AWG
<a href="#">19154-0028</a>	25	Insulated Butt Splice Connector, 12-10 AWG
<a href="#">19160-0002</a>	25	Insulated Nylon Closed-end Connector, 16-14 AWG
<a href="#">19160-0012</a>	25	Insulated Closed-end Splice Connector, 22-14 AWG
<a href="#">19216-0003</a>	15	Insulated Multi-Lock Connector, 16-14 AWG
CT-4071-1R	1	Universal Hand Crimping Tool, 22-10 AWG