
LED LENS CAPS

Designed for use with T-1 or T-1 3/4 LEDs, these Lens Caps are available in round or square configurations. They snap-mount through the front panel for easy, light-finger pressure, intsallation. The LED is inserted into the cap from behind the panel and held securely in place.


The Lens Cap protects the LED from physical damage while guarding the components from electrostatic discharge (ESD), up to 16KV. More economical than indicator light assemblies, the caps feature striated lines and fresnel rings which permit up to 180 viewing angles with either diffused or non-diffused LED's. They provide exceptionally high contrast and visibility.





MATERIAL: Polycarbonate Available in Red, Green, Yellow and Clear

.290 [7.4] .150



[4.9] DIA. .290 [7.4] .060 [1.52] .171 [4.4] DIA.




FIG. 1 T-1

FIG. 2 T-1 3/4

STANDARD HEIGHT

CAT. NO.	COLOR	FIG. No.	LED Size	MTG. HOLE Size	MIN. MTG. Centers	PANEL THICKNESS
8650	RED	1	T-1	.171 (4.3)	.250 (6.4)	.031062 (.79/1.57)
8651	GREEN					
8652	YELLOW					
8653	CLEAR					
8662	RED	2	T-1 3/4	.250 (6.4)	.375 (9.5)	.062125 (1.57/3.18)
8663	GREEN					
8664	YELLOW					
8665	CLEAR					

FIG. 3 T-1

FIG. 4 T-1 3/4

LOW PROFILE

CAT. NO.	COLOR	FIG. NO.	LED Size	MTG. HOLE Size	MIN. MTG. Centers	PANEL Thickness
8656	RED	3	T-1	.171 (4.3)	.250 (6.4)	.062125 (1.57/3.18)
8657	GREEN					
8658	YELLOW					
8659	CLEAR					
8668	RED	4	T-1 3/4	.250 (6.4)	.375 (9.5)	.031 - 250 (.79/6.4) (See Note)
8669	GREEN					
8670	YELLOW					
8671	CLEAR					

SQUARE CAPS






FIG. 5 T-1 3/4

STANDARD HEIGHT

CAT. NO.	COLOR	FIG. No.	LED Size	MTG. HOLE Size	MIN. MTG. CENTERS	PANEL THICKNESS
8680	RED	5	T-1 3/4	.250 (6.4) SQUARE	.375 (9.5)	.062125 (1.57/3.18)
8681	GREEN					
8682	YELLOW					
8683	CLEAR					





LOW DDOELLE

FIG. 6 T-1


FIG. 7 T-1 3/4

LUW PRU	LOW PROFILE						
CAT. NO.	COLOR	FIG. No.	LED SIZE	MTG. HOLE Size	MIN. MTG. CENTERS	PANEL Thickness	
8674	RED	6	T-1	.171 (4.3)	.250 (6.4)	.062125 (1.57/3.18)	
8675	GREEN						
8676	YELLOW						
8677	CLEAR						
8686	RED						
8687	GREEN	7	T-1 3/4	.250 (6.4)	.375 (9.5)	.031250 (.79/6.4) (See Note)	
8688	YELLOW	'					
8689	CLEAR					(SEE MOLE)	

Note: When mounting T-1 3/4 Low Profile Caps (Fig. 4 or Fig. 7) in panels .125 (3.2) thick or less a spacer must be used. **Spacer CAT. NO. 8692 MATERIAL:** White Nylon .360 (9.1) 0.D. \times 1/4 l.D. \times 1/8 Lg.

"SNAP-IN" T-1 & T-1 3/4 LED HOLDERS


Designed for use with T-1 or T-1 3/4 LED's in .060 (1.52) - .070 (1.78) thick panels. The holder snaps into the front panel with easy, light-finger pressure. The LED snaps into the holder from behind the panel and is held securely in place.





MATERIAL: Nylon 6/6, Black

CAT. NO.	LED SIZE	A	В	C	MTG. HOLE Size
8309	T-1	.114 (2.9)	.232 (5.9)	.188 (4.8)	.171 (4.3)
8310	T-1 3/4	.200 (5.0)	.315 (8.0)	.274 (6.9)	.250 (6.4)



KEYSTONE