

Product data sheet

Characteristics

H361

SWITCH FUSIBLE HD 600V 30A 3P NEMA1

Product availability: Stock - Normally stocked in distribution facility



Main

Commercial Status	Commercialised
Product or component type	Single Throw Safety Switch
Line Rated Current	30 A
Product certifications	UL listed
NEMA degree of protection	NEMA 1 steel
Device composition	None
Disconnecter device type	Fusible disconnect
Short-circuit current	200 kA R, J or L 10 kA H or K
Device mounting	Surface
Number of poles	3
Electrical connection	Lugs
Series name	Heavy duty
System Voltage	600 V AC/DC
AWG gauge	14...6 AWG copper 12...6 AWG aluminium

Ordering and shipping details

Category	00008 - H&HU, 2&3P, N1, 30-200A
Discount Schedule	DE1
GTIN	00785901481843
Nbr. of units in pkg.	1
Package weight(Lbs)	8.04
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	US

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Will be Compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold

Contractual warranty

Period	18 months
--------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.