

<b>Specification</b>	<b>NOTE</b>	<b>PRB-04</b>
Attenuation Ratio	[1]	10:1 & 1:1 (switchable)
Bandwidth		5MHz & 60 MHz
Rise Time		70ns & 6ns
Input Resistance		1M & 10M
Input Capacitance		18pF
Compensation Range		10 to 30 pF
Maximum Voltage		600V CAT I, 300V CAT II(DC+AC peak)
Working Voltages		10mV to 110V
Device Connection		BNC
Power Requirement		None, Passive
Operating Temperature		0 °C to 50 °C
Humidity		85% RH or less (at 35°C)
Safety		Meets EN61010-031 CAT II
Cable Length		1.0M
Compliance		RoHS, CE
Weight	[2]	60 g

FA27K-09

[1] Attenuation ratio is switchable from 1:1 and 10:1 on some models.

[2] Product weight in pack with kit accessories.