


**ROHS**

NO.	DATE	DESCRIPTION	APPROVAL
1.0			
2.0			



P1	P2	P1	P2
Pin1 — violet — test clip(black)	Pin6 — blue — test clip(black)		
Pin2 — yellow — test clip(black)	Pin7 — white — test clip(black)		
Pin3 — orange — test clip(black)	Pin8 — black — test clip(black)		
Pin4 — green — test clip(black)	Pin9 — grey — test clip(black)		
Pin5 — brown — test clip(black)	Pin10 — red — test clip(red)		

Item	Title	Specification	Q'TY	Note
⑤	Conn	Test clip red color	1PCS	
④	Conn	Test clip black color	9PCS	
③	TR	TJC8 type pitch2.54mm crimp terminal materials:phosphorous bronze tin-plated	10PCS	
②	HSG	TJC8 type housing pitch2.54mm*1Pin materials:pa66 black color	1PCS	
①	Wire	UL1007 26AWG(7/0.127TS) OD:1.3mm color:violet/yellow/orange/green/brown/blue/red/black/grey/white	10PCS	

DRAWING:	TOLERANCE .X:=±0.50 .XX:=±0.30 .XXX:=±0.10		
	CHECKED:		
APPROVAL:	UNIT: MM	CUSTOMER	REV: 1.0
	SCALE: N/A	PART NO: CLP-02	
	SHEET: 1/1	CUSTOMER P/N:	SIZE: A4