


PRODUCT SPECIFICATION

Brand	C.K
Product Range	Sabretooth trade saws
Catalogue number	840 & 940
Date	26/05/2015

<p>Range Description High performance hand saw range</p>				
<p>Features & Benefits</p> <p>Featuring triple ground 'turbo cut' hardpoint teeth, the Sabretooth Trade saws offer advanced cutting performance and an extended working life</p> <ul style="list-style-type: none"> • Universal tooth pitch for a wide range of materials • Triple ground 'turbo cut' teeth for advanced cutting performance • Offset teeth for reduced friction & greater waste removal • 0.85mm premium grade CK5 steel blade for maximum power transfer • 45 & 90° angle guides for ease of marking out • Dual Component cushion grip handle for comfort and control • Stay sharp, hard point teeth for an extended working life 				
Item Number	Item Description	EAN No	Commodity code	Carton Qty
T0840 20	Sabretooth Trade Saw Universal 20in	5013969810066	82021000	10
T0840 22	Sabretooth Trade Saw Universal 22in	5013969810073	82021000	10
T0940 22	Sabretooth Trade Saw Fine Cut 22in	5013969810080	82021000	10

Technical product information	<p>Blade Material - SK5 Alloy steel</p> <p>Teeth Triple ground edge, hard-point teeth. 840 series – 7tpi, 8ppi 940 series – 9tpi, 10ppi</p> <p>Handle Black plastic injection moulded with yellow TPE soft grip overmould.</p> <p>Application Universal tooth pitch for a wide range of materials including timber, chipboard, plywood and plastics.</p>
Standards compliance	None applicable
User health and safety information	Users are advised to wear safety goggles and protective gloves
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	The Sabretooth saws are guaranteed for life against imperfect materials or workmanship The teeth will wear in use and such wear is not covered under the terms of the warranty
Country of origin	China

Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T0840 20	600	37	145	408	600	37	145	435
T0840 22	645	37	145	432	645	37	145	463
T0940 22	645	37	145	438	645	37	145	469

Item	Shelf box (secondary packaging)				Euro Pallet data		Wi x Hi
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high	
T0840 20	650	200	155	4470	4	3	
T0840 22	650	200	155	5023	4	3	
T0940 22	650	200	155	5023	4	3	

Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T0840 20	8	Blade Cover	27	Sleeve			450	Box
T0840 22	8	Blade Cover	31	Sleeve			477	Box
T0940 22	8	Blade Cover	31	Sleeve			477	Box