



Product Data Sheet

Twin Reading Thermometer

Electronic thermometer with max min feature and high/low temperature alarm setting. Ideally suited to read temperature in a fridge or freezer or outdoor temperature and room temperature simultaneously. Magnet fixture.

Product Specifications

Room Temperature Range: -20 to +70°C&F (switchable)
Fridge/Freezer Range: -50 to +70°C&F (switchable)
Resolution: 0.1°C
Reading Update: 10 seconds
Accuracy: Indoor: -20/70°C +/-1°C
Outdoor: -50/-20°C +/-1.5°C & -20/70°C +/-1°C
+/-5%RH
Battery: AAA x 1pc
Battery Life: Approx 1 year
CE: Approved
ROHS/WEEE: Approved
Hazard Information (SDS): See www.brannan.co.uk for information

Product Weight: Packaged - 79g
Unpackaged - 62g (including battery)
Product Dimensions: Packaged - 170 x 110 x 35mm
Unpackaged - 63 x 63 x 15mm
LCD Dimensions: 21mm x 47mm
Probe Length: 2m
Display Card Weight: 9g
Display Card Dimensions: 170 x 110 x 0.5mm
Display PVC Blister Weight: 8g
Display PVC Blister Dimensions: 170 x 110 x 35mm



| Description | Range | Divisions | Barcode | Product No |
|--------------------------|-------------|-----------|-----------------|------------|
| Twin Reading Thermometer | -50 +70°C&F | 0.1°C | 5 011405 224200 | 22/420/3 |

Please note: all information on this data sheet is correct at the time of printing, but our policy is one of continuous product development. We reserve the right to change specification without notice.

PDS 0197:14:R2



Brannan Thermometers & Instrumentation

Leconfield Industrial Estate • Cleator Moor • Cumbria • CA25 5QE • UK

tel: +44 (0)1946 816600 fax: +44 (0)1946 816625 email: sales@brannan.co.uk web: www.brannan.co.uk

