



Product Data Sheet

K-Type Probe for Gas & Air

K-type probe to widen the temperature range of compatible products and to improve access to objects where more remote reading is required due to limited access or for safety reasons.

This model is suitable for measuring temperature of gas and air.

Product Specifications

Temperature Range:	-50 to 800°C&F
Accuracy:	+/- 1.5°C
CE & ROHS/WEEE:	Approved
Hazard Information (SDS):	See www.brannan.co.uk for information
Probe	165mm Stainless steel probe with 133mm handle
Product Weight:	Packaged - 125g Unpackaged - 91g
Product Dimensions:	Packaged - 428 x 82 x 33mm
Display Blister Weight:	24g
Display Card Weight:	10g



Description	Barcode	Product No
K-type Probe for Gas & Air	5 011405 386915	38/691/0

Please note: all information on this data sheet is correct at the time of printing, but our policy is one of continuous product development. We reserve the right to change specification without notice.

PDS 0125:14:R2

Brannan Thermometers & Instrumentation

Leconfield Industrial Estate • Cleator Moor • Cumbria • CA25 5QE • UK

tel: +44 (0)1946 816600 fax: +44 (0)1946 816625 email: sales@brannan.co.uk web: www.brannan.co.uk

